

Datasheet

RHOA polyclonal antibody (A01)

Catalog Number: H00000387-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a partial recombinant RHOA.

Immunogen: RHOA (AAH01360.1, 91 a.a. ~ 190 a.a) partial recombinant protein with GST tag.

Sequence:

SLENIPEKWTPEVKHFPCPNVPIILVGNKKDLRNDHTR
RELAKMKQEPVKPEEGRDMANRIGAFGYMECSAKTK
DGVREVFEMATRAALQARRGKKKSGC

Host: Mouse

Reactivity: Human

Applications: ELISA, WB-Re

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 387

Gene Symbol: RHOA

Gene Alias: ARH12, ARHA, RHO12, RHOH12