

Datasheet

RHOA monoclonal antibody (M06), clone 1C10

Catalog Number: H00000387-M06

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a full length recombinant RHOA.

Clone Name: 1C10

Immunogen: RHOA (AAH01360, 1 a.a. ~ 193 a.a)
full-length recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

MAAIRKKLVIVGDGACGKTCLLIVFSKDQFPEVYVPTVF
ENYVADIEVDGKQVELALWDTAGQEDYDRLRPLSYDP
TDVILMCFSIDSPDSLENIPEKWTPEVKHFCPNVPIILVG
NKKDLRNDDEHTRRELAKMKQEPVKPEEGRDMANRIG
AFGYMECSAKTKDGVREVFEMATRAALQARRGKKKS
GCLVL

Host: Mouse

Reactivity: Human

Applications: ELISA, IF, S-ELISA, WB-Ce, WB-Re
(See our web site product page for detailed applications
information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG1 lambda

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 387

Gene Symbol: RHOA

Gene Alias: ARH12, ARHA, RHO12, RHOH12