

Datasheet

RNF113B purified MaxPab mouse polyclonal antibody (B01P)

Catalog Number: H00140432-B01P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human RNF113B protein.

Immunogen: RNF113B (NP_849192.1, 1 a.a. ~ 322 a.a) full-length human protein.

Sequence:

MAAPPSPGRTADQADQVCTFLFKKPGRKGAAGLRKR
PACDPEHGESSSSGDEGDTVAQPPRVAPRPRGLHSW
QKAAHGDRRGEEAAPESLDVVYRSTRSAKPVGPEDM
GATADFEQDTEKEHHTPTILKCSQRVQEALRGREHDH
IYRGIHSYLRYLKPKDTSMGNSSSGMARKGPIRAPGHL
RATVRWDYQPDICKDYKETGFCGFGDSCKFLHDRSD
YKLGWEIERELEEGRYCICEDENHEVGSEEEEIPFRCF
ICRQAFQNPVVTCKRHYFCESCALEHFRATPRCYICD
QPTGGIFNPAKELMAKLQKLQAAEGKKR

Host: Mouse

Reactivity: Human

Applications: IF, WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 140432

Gene Symbol: RNF113B

Gene Alias: MGC26599, RNF161, ZNF183L1, bA10G5.1