

Datasheet

DYNLL2 monoclonal antibody (M04), clone 1G7

Catalog Number: H00140735-M04

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a partial recombinant DYNLL2.

Clone Name: 1G7

Immunogen: DYNLL2 (NP_542408, 1 a.a. ~ 72 a.a)
partial recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

MSDRKAVIKNADMSQDAVDCATQAMEKYNIEK
DIAAYIKKEFDKKYNPTWHCIVGRNFGSYVTHETKH

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Re

(See our web site product page for detailed applications
information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG2b Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 140735

Gene Symbol: DYNLL2

Gene Alias: DNCL1B, Dlc2, MGC17810