

Datasheet

LDHAL6A purified MaxPab mouse polyclonal antibody (B01P)

Catalog Number: H00160287-B01P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human LDHAL6A protein.

Immunogen: LDHAL6A (AAH14340.1, 1 a.a. ~ 234 a.a) full-length human protein.

Sequence:

MATIKSELIKNFAEEEEAIHHNKISIVGTGSGVGVACAI SILL
KGLSDELVLVDVDEGKLKGETMDLQHGSPFMKMPNIV
SSKDYLVTANSNLVIITAGARQKKGETRLDLVQRNVSIF
KLMIPNITQYSPHCKLLIVTNPVDILTYVAWKLSGF PKN
RVIGSGCNLDSARFRYFIGRLGIHSESCHGLILGEHG
DSSVPVWSGVNIAGVPLKDLNPDIGTDKDPEQWENVH
KKK

Host: Mouse

Reactivity: Human, Rat

Applications: WB-Ce, WB-Ti, WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 160287

Gene Symbol: LDHAL6A

Gene Alias: MGC23940