

Datasheet

LONRF2 monoclonal antibody (M01), clone 1C7

Catalog Number: H00164832-M01

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a partial recombinant LONRF2.

Clone Name: 1C7

Immunogen: LONRF2 (NP_940863, 1 a.a. ~ 108 a.a)
partial recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

MKNYEQALQDASAACQNEPLLIKGHQVKAQALSGLGR
SKEVLKEFLYCLALNPECNSVKKEAQKVMCEVLFSATA
NVHENLTSSIQSRLKAQGHSHMNAQALLEEGDA

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA

(See our web site product page for detailed applications
information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 164832

Gene Symbol: LONRF2

Gene Alias: FLJ45273, MGC126711, MGC126713,
RNF192