

Datasheet

DHRX MaxPab mouse polyclonal antibody (B01)

Catalog Number: H00207063-B01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human DHRX protein.

Immunogen: DHRX (NP_660160.1, 1 a.a. ~ 330 a.a.) full-length human protein.

Sequence:

MSPLSAARAALRVYAVGAAVILAQLLRRCRGGFLEPVF
PPRPDRVAIVTGGTDGIGYSTAKHLARLGMHVIIAGNN
DSKAKQVVSKEETLNDKVEFLYCDLASMTSIRQFVQ
KFKMKKIPLHLINNAGVMMVPQRKTRDGFEEHFGLN
YLGHFLLTNLLDNLKESGSPGHSARVTVSSATHYVA
ELNMDDLQSSACYSPPHAAQAQSKLALVLFTYHLQRL
AAEGSHVTANVVDPGVVNTDLYKHVFWATRLAKKLLG
WLLFKTPDEGAWTSIYAAVTPELEGVGGRYLYNEKET
KSLHVTYNQKLQQQLWSKSCMTGVLDVTL

Host: Mouse

Reactivity: Human

Applications: IF, WB-Ti, WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: No additive

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 207063

Gene Symbol: DHRX

Gene Alias: CXorf11, DHR5X, DHR5Y, DHRXY, DHR5Y, SDR46C1