

Datasheet

MGC15730 polyclonal antibody (A01)

Catalog Number: H00084966-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a partial recombinant MGC15730.

Immunogen: MGC15730 (NP_116269, 201 a.a. ~ 300 a.a) partial recombinant protein with GST tag.

Sequence:

ASSGPLQDSRPFRSLLHRDLDDTKMQKSLSLLDAENR
GGRPYTERPSRGLTPDPNILLQPTTENIPETVVSREFP
RWVHSAEPTYFLRHSRTPSSDGTVE

Host: Mouse

Reactivity: Human, Mouse

Applications: ELISA, WB-Ce, WB-Re

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 84966

Gene Symbol: IGSF21

Gene Alias: FLJ41177, MGC15730