

Datasheet

ARL8A monoclonal antibody (M02), clone 3H4

Catalog Number: H00127829-M02

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a full-length recombinant ARL8A.

Clone Name: 3H4

Immunogen: ARL8A (AAH15408, 1 a.a. ~ 186 a.a)
full-length recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

MIALFNKLLDWFKALFWKEEMELTLVGLQYSGKTTFVN
VIASGQFNEDMIPTVGFNMRKITKGNVTIKLWDIGGQP
RFRSMWERYCRGVSAIVYMVDAADQEKIEASKNELHN
LLDKPQLQGIPVLVLGNKRDLPALDEKELIEKMNL
SAIQDREICCYSISCKEKDNIDITLQWLIQHKSRRS

Host: Mouse

Reactivity: Human

Applications: ELISA, IF, WB-Re

(See our web site product page for detailed applications
information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG2b Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 127829

Gene Symbol: ARL8A

Gene Alias: ARL10B, FLJ45195, GIE2