

## Datasheet

### Kcnp4 polyclonal antibody

**Catalog Number:** PAB16892

**Regulation Status:** For research use only (RUO)

**Product Description:** Rabbit polyclonal antibody raised against synthetic peptide of Kcnp4.

**Immunogen:** A synthetic peptide (conjugated with KLH) corresponding to mouse Kcnp4.

**Sequence:** KTSSPAIQNSV

**Host:** Rabbit

**Reactivity:** Mouse

**Applications:** EIA, WB

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Form:** Lyophilized

**Recommend Usage:** EIA (1:300000)

Western Blot (1:1000)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** Lyophilized from 10 mM PBS

**Storage Instruction:** Store at -20°C on dry atmosphere.

After reconstitution with deionized water, store at -20°C or lower.

Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 80334

**Gene Symbol:** Kcnp4

**Gene Alias:** AV032399, Calp, Calp250, KChIP4