

Datasheet

HMGN2 polyclonal antibody

Catalog Number: PAB18390

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against synthetic peptide of HMGN2.

Immunogen: A synthetic peptide corresponding to human HMGN2.

Host: Rabbit

Reactivity: Human, Mouse, Rat

Applications: ELISA, IF, IHC-P
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Specificity: This antibody is specific to HMGN2.

Form: Liquid

Purification: Affinity purification

Concentration: 1 mg/mL

Recommend Usage: Immunohistochemistry
(1:50-1:100)
Immunofluorescence (1:500-1:1000)
ELISA (1:5000)
The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, 150mM NaCl, pH 7.4 (50% glycerol, 0.02% sodium azide)

Storage Instruction: Store at -20°C.
Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 3151

Gene Symbol: HMGN2

Gene Alias: HMG17, MGC5629, MGC88718