

Datasheet

NEK2 monoclonal antibody (M02), clone 2F9

Catalog Number: H00004751-M02

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a partial recombinant NEK2.

Clone Name: 2F9

Immunogen: NEK2 (AAH43502, 331 a.a. ~ 445 a.a)
partial recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

EQELCVRERLAEDKLARAENLLKNYSLLKERKFLSLAS
NPELLNLPSSVIKKKVHFSGESKENIMRSENSESQ LTS
KSKCKDLKKRLHAAQLRAQALSDIEKNYQLKSRQILGM
R

Host: Mouse

Reactivity: Human, Rat

Applications: ELISA, IF, S-ELISA, WB-Ce, WB-Re
(See our web site product page for detailed applications
information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 4751

Gene Symbol: NEK2

Gene Alias: HsPK21, NEK2A, NLK1