

Datasheet

ANAPC11 polyclonal antibody

Catalog Number: PAB19240

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against synthetic peptide of ANAPC11.

Immunogen: A synthetic peptide corresponding to 18 amino acids near internal region of human ANAPC11.

Host: Rabbit

Reactivity: Human, Mouse, Rat

Applications: ELISA, WB-Ce
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Peptide affinity purification

Concentration: 1 mg/mL

Recommend Usage: Western Blot (1-2 ug/mL)
The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS (0.02% sodium azide)

Storage Instruction: Store at 4°C for three months. For long term storage store at -20°C.
Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 51529

Gene Symbol: ANAPC11

Gene Alias: APC11, Apc11p, HSPC214, MGC882