

## Datasheet

### HSPA12A polyclonal antibody

**Gene Symbol:** HSPA12A**Catalog Number:** PAB20545**Gene Alias:** FLJ13874, KIAA0417**Regulation Status:** For research use only (RUO)**Product Description:** Rabbit polyclonal antibody raised against recombinant HSPA12A.**Immunogen:** Recombinant protein corresponding to amino acids of human HSPA12A.**Sequence:**KLLVKDGTRWCTDVFDKFISADQSVLALGELVKRSYTP  
AKPSQLVIVINIYSSEHDNVSFITDPGVKKCGTLRLDLT  
GTSGTAVPARREIQTLMQFGDTEIKATAIDIATSKSVKV  
GID**Host:** Rabbit**Reactivity:** Human**Applications:** IHC-P, WB

(See our web site product page for detailed applications information)

**Protocols:** See our web site at<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols**Form:** Liquid**Purification:** Antigen affinity purification**Isotype:** IgG**Recommend Usage:** Immunohistochemistry

(1:50-1:200)

Western Blot (1:250-1:500)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 259217