

## Datasheet

### AOF1 polyclonal antibody

**Gene Alias:** C6orf193, DKFZp686I0412, FLJ33898, FLJ34109, FLJ43328, bA204B7.3, dJ298J15.2

**Catalog Number:** PAB22537

**Regulation Status:** For research use only (RUO)

**Product Description:** Rabbit polyclonal antibody raised against recombinant AOF1.

**Immunogen:** Recombinant protein corresponding to amino acids of human AOF1.

**Sequence:**

CEQLGISMHKFGERCDLIQEGGRITDPTIDKRMDFFHN  
ALLDVVSEWRKDKTQLQDVPLGEKIEEIYKAFIKESGIQ  
FSELEGQVLQFHLSNLE

**Host:** Rabbit

**Reactivity:** Human

**Applications:** IHC-P

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Form:** Liquid

**Purification:** Antigen affinity purification

**Isotype:** IgG

**Recommend Usage:** Immunohistochemistry (1:20-1:50)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.  
Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 221656

**Gene Symbol:** AOF1