

Datasheet

RMND1 polyclonal antibody

Gene Symbol: RMND1

Catalog Number: PAB22548

Gene Alias: C6orf96, FLJ20627, MGC117362,
MGC149570, MGC88260, RMD1, bA351K16,
bA351K16.3

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant RMND1.

Immunogen: Recombinant protein corresponding to amino acids of human RMND1.

Sequence:

LKAGKKVKLSHEEVMQKIGELFALRRHINLSSDFLITPD
FYWDRENLEGLYDKTCQFLSIGRRVKVMNEKLQHCM
EL

Host: Rabbit

Reactivity: Human

Applications: IHC-P, WB

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry

(1:200-1:500)

Western Blot (1:250-1:500)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 55005