

Datasheet

IKIP polyclonal antibody

Gene Symbol: IKIP

Catalog Number: PAB23328

Gene Alias: FLJ31051

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant IKIP.

Immunogen: Recombinant protein corresponding to amino acids of human IKIP.

Sequence:

LESTESILQEATSSMSLMTQFEQEVSNLQDIMHDIQNN
EEVLTQRMQSLNEKFQNITDFWKRSL EEMNINTDIFKS
EAKHIHSQVTVQIN

Host: Rabbit

Reactivity: Human

Applications: IHC-P

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry

(1:500-1:1000)

Western Blot (1:250-1:500)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 121457