

## Datasheet

### C20orf196 polyclonal antibody

**Gene Alias:** FLJ25067, RP4-784N16.1

**Catalog Number:** PAB23490

**Regulation Status:** For research use only (RUO)

**Product Description:** Rabbit polyclonal antibody raised against recombinant C20orf196.

**Immunogen:** Recombinant protein corresponding to amino acids of human C20orf196.

**Sequence:**

NNSWTAENFWLDPVKGQSEKEEDDGLRKSLDRFYE  
MFGHPQPGSANSLSASVCKCLSQKITQLRGQES

**Host:** Rabbit

**Reactivity:** Human

**Applications:** IHC-P, WB-Tr

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Form:** Liquid

**Purification:** Antigen affinity purification

**Isotype:** IgG

**Recommend Usage:** Immunohistochemistry

(1:50-1:200)

Western Blot (1:250-1:500)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 149840

**Gene Symbol:** C20orf196