

Datasheet

DNAJC17 polyclonal antibody

Gene Symbol: DNAJC17**Catalog Number:** PAB23714**Gene Alias:** FLJ10634**Regulation Status:** For research use only (RUO)**Product Description:** Rabbit polyclonal antibody raised against recombinant DNAJC17.**Immunogen:** Recombinant protein corresponding to amino acids of human DNAJC17.**Sequence:**AVVEFATVKAAELAVQNEVGLVDNPLKISWLEGQPQD
AVGRSHSGLSKGSLSERDYESLVMMRMQRQAERQ
QLIARMQQEDQ**Host:** Rabbit**Reactivity:** Human**Applications:** IHC-P, WB

(See our web site product page for detailed applications information)

Protocols: See our web site at<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols**Form:** Liquid**Purification:** Antigen affinity purification**Isotype:** IgG**Recommend Usage:** Immunohistochemistry

(1:200-1:500)

Western Blot (1:250-1:500)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 55192