

Datasheet

HN1 monoclonal antibody (M01), clone 2C8

Catalog Number: H00051155-M01

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a full length recombinant HN1.

Clone Name: 2C8

Immunogen: HN1 (AAH01420, 1 a.a. ~ 154 a.a)
full-length recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

MTTTTTFKGVDPNSRNSSRVL RPPGGGSNFS LGFDEP
TEQPVRKNKMASNIFGTPEENQASWAKSAGAKSSGG
REDLESSGLQRRNSSEASSGDFLDLKGEGDIHENVDT
DLPGSLGQSEEKPVPAAPVPSPVAPAPMPSRRNPPG
GKSSLVLG

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Re
(See our web site product page for detailed applications
information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG1 kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 51155

Gene Symbol: HN1

Gene Alias: ARM2, HN1A