

INTRODUCING BDH® HiPerSolv CHROMANORM SOLVENTS FOR HPLC

BDH® CHEMICALS -
HERE WE
G-R-O-W AGAIN!



EXPERIENCE | VALUE | RESULTS

The new BDH® HiPerSolv CHROMANORM Solvents Provide Comprehensive Solutions for your HPLC Applications

VWR is proud to introduce the newest addition to the exclusive family of high-quality, competitively-priced BDH Chemicals - high purity solvents for HPLC applications. Manufactured at a state-of-the-art European ISO 9001 - ISO 14001 solvent production facility, the initial range of six of the most popular HPLC solvents provides an unparalleled combination of performance and price for even the most demanding liquid chromatography applications. Packaged in standard 4L North American bottles and 4 x 4L cases, these solvents:

- Are designed to meet demanding HPLC and UV/Vis analytical and quality control requirements
- Are filtered down to 0.2µm level and bottled under nitrogen
- Include super-gradient grade acetonitrile, with >95% UV transmittance at 200nm and <30ppm water content
- Feature tamper-evident caps for added peace of mind
- Carry Globally Harmonized System (GHS) labeling to help with compliance
- Feature environmentally-friendly corrugate/pulp case inserts that are fully recyclable

Visit ca.vwr.com/bdh for complete specifications, certificates of analysis, and SDS's.



BDH® Solvents, 4L

Description	Cat. No.	Each	Case of 4
Acetonitrile	CABDH83639.400	303.82	1154.56
Dichloromethane (DCM)	CABDH23373.400	184.44	700.85
Hexane	CABDH24575.400	187.97	714.29
Isopropyl Alcohol (IPA)	CABDH20880.400	193.95	736.97
Methanol	CABDH20864.400	118.22	449.25
Water	CABDH23595.400	102.89	391.00



Left to Right: VWR Chromatography Vials, VWR Syringe Filters, VWR Storage Cabinets, VWR Hazmat Spill Response Kit, VWR Bottle Tote Safety Carriers

VWR® Chromatography Vials

Description	Size	Cat. No.	Price
Vial with Versatile Dual Crimp-Top/Snap-Cap, Clear Glass, I-D™ Fused Insert	2 mL	66009-822	Pk.100/ 31.13
Vial with Wide Opening Crimp-Top, Clear Glass	2 mL	66010-539	Pk.100/ 34.18
Accessories			
Seal, Aluminum with Clear PTFE/Synthetic Red Rubber Septa	11 mm	46610-754	Pk.100/ 28.43
Snap Cap, Pre-Slit PTFE/Natural Silicone	11 mm	82028-418	Cs.1000/ 522.75

VWR® Syringe Filters

Syringe Filters with Polypropylene Housing, 25 mm Dia.			
	Pore Size, µm	Cat. No.	Case of 100
Nylon	0.2	CA28145-487	204.04
Nylon	0.45	CA28145-489	204.04
PTFE	0.2	CA28145-495	341.85
PTFE	0.45	CA28145-497	341.85

VWR® Storage Cabinets

Cabinets for Flammables and Corrosives, 30 Gal.		D x W x H, cm	Cat. No.	Each
Manual Close		45.7 x 109.2 x 111.8	97044-198	1478.40
Self Close		45.7 x 109.2 x 111.8	97044-206	1603.84
Self Close, Bi-fold		45.7 x 109.2 x 111.8	97044-214	1786.88

VWR® Hazmat Spill Response Kit

Description	Cat. No.	Each
Absorbency up to 34.1 L (9 gal.) of Acids, Caustics, and Bases	89168-998	81.75

VWR® Large Bottle Tote Safety Carriers

Color	Cat. No.	Each
Red	56608-970	115.39
White	56608-975	115.39
Black	56608-980	115.39



1.800.932.5000 | vwr.com

Prices and product details are current when published; subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in Canadian dollars unless otherwise noted. Offers valid in Canada, void where prohibited by law or company policy, while supplies last. | VWR, the VWR logo and variations on the foregoing are registered (®) or unregistered trademarks and service marks, of VWR International, LLC and its related companies. All other marks referenced are registered by their respective owner(s). | Visit vwr.com to view our privacy policy, trademark owners and additional disclaimers. ©2014 VWR International, LLC. All rights reserved.