



JACKETED REACTORS KILO SCALE

10L, 15L & 20L Base Systems

Universal open frame stand design allows for maximum clearance and access to the ports on the head. To allow for scale up, the frame has been designed to be fitted with vessels up to 50L in size. Simply select the stand motor mounting configuration based upon the desired type of motor. Then select the motor and shaft coupling that corresponds with the matching motor mount. Once the stand and motor have been selected complete the system by adding additional accessories to meet your applications requirements.

Base Jacketed Systems

- Working Temp Range (°C): -60 to 200
- Working Pressure Range (Torr): Atm to 0
- Max Jacket Pressure (PSI): 8
- Dimensions (in.): 27.5 x 24.25 x 82.25
- Wetted Surfaces: Borosilicate glass, PTFE

Order


• Motor Mounts: Rod or Flange

Select a base system dependent on desired capacity and motor mounting type.

Capacity (L)	Base Systems for Rod Mounted Motors	Base Systems for Flange Mount Motors
10	10767-518	10768-078
15	10767-860	10767-200
20	10767-202	10767-204

Base Systems include the following components:

No.	Description	Qty.	Code
1	10-20L Universal Stand w/Mount for Rod Mount Motors	4	_
	10-20L Universal Stand w/Mount for Flange Mount Motors		-
	10L Jacketed Flask	1	10768-114
2	15L Jacketed Flask		10768-116
	20L Jacketed Flask		10768-118
	200mm, 5 Neck Head	1	10767-300
	200mm CAPFE O-Ring	1	89061-172
3	200mm Quick-release Clamp	1	89055-114
	60mm Glass Cap	1	89078-304
	60mm CAPFE O-Ring	1	89061-162
	60mm Quick-release Clamp	1	89055-106
	19mm PTFE Ace-Thred Bearing	1	89061-908
	19mm Glass Stirring Shaft, 36" Length	1	89061-992
4	19mm Shaft Collar	1	89235-696
	5 1/2in. O.D. Anchor Style Agitator	1	89062-146
	5in. O.D. 45° Agitator	1	10767-330
-	Flush Seal Drain Valve w/CAPFE O-Ring	1	89054-660
5	2in. Beaded Pipe Coupling	1	89064-666
6	1in. Beaded Pipe Coupling	2	89064-662





1.800.932.5000 | vwr.com

Head Port Configuration

Prices and product details are current when published; subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR makes no claims or warranties concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in US dollars unless otherwise noted. Offers valid in US, void where prohibited by law or company policy, while supplies last. | VWR, the VWR logo and variations on the foregoing are registered (®) or unregistered trademarks and service marks, of VWR International, LLC and its related companies. All other marks referenced are registered by their respective owner(s). | Visit vw.com to view our privacy policy, trademark owners and additional disclaimers. @2015 VWR International, LLC. All rights reserved.