



JACKETED REACTORS KILO 30L & 50L Base Systems

Universal open frame stand design allows for maximum clearance and access to the ports on the head. To allow for scale up, the frame has been designed to be fitted with vessels from 10L to 50L in size. Simply select the stand motor mounting configuration based upon the desired type of motor. Then select the motor and shaft coupling that corresponds with the matching motor mount. Once the stand and motor have been selected complete the system by adding additional accessories to meet your applications requirements.

Base Jacketed Systems

- Working Temp Range (°C): -60 to 200
- Working Pressure Range (Torr): Atm to 50
- Max Jacket Pressure (PSI): 8

WR

We Enable Science


- Dimensions (in.): 27.5 x 24.25 x 82.25
- Wetted Surfaces: Borosilicate glass, PTFE
- Motor Mounts: Flange Mount


Select a base system dependent on desired capacity and motor mounting type.

Capacity (L)	Base Systems for Flange Mount Motors
30	10768-080
50	10768-082

Base Systems include the following components:

No.	Description	Qty.	Order Code
1	30-50L Universal Stand w/Mount for Flange Mount Motors	1	-
2	30L Jacketed Flask	-	10768-120
2	50L Jacketed Flask	1	10768-122
•••••	300mm, 7 Neck Head	1	10767-302
	300mm PTFE Flat Gasket	1	89055-286
0	300mm KF Flat Flange Clamp	1	89055-274
3	100mm Glass Cap	1	89078-306
	100mm CAPFE O-Ring	1	89061-166
	100mm Quick-release Clamp	1	89055-110
	28mm PTFE Ace-Thred Bearing	1	89061-896
	28mm Glass Stirring Shaft, 45in. Length	1	89062-020
4	28mm Shaft Collar	1	89235-698
	28mm Shaft Coupling	1	10767-942
	8in. O.D. Anchor Style Agitator	1	71001-578
	6in. O.D. 45° Agitator	1	89062-176
	Flush Seal Drain Valve w/CAPFE O-Ring and Pin	1	71001-526
5	2in. Beaded Pipe Coupling	1	89064-666
6	1 1/2in. Beaded Pipe Coupling	2	89064-664





1.800.932.5000 | vwr.com

Prices and product details are current when published; subject to change without notice. [Certain products may be limited by federal, state, provincial, or local regulations.] VWR makes no daims or warranties concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in US dollars unless otherwise noted. Offers valid in US, void where prohibited by law or company policy, while supplies last.] VWR, the VWR logo and variations on the foregoing are registered (so or unregistered trademarks and service marks, of VWR International, LLC. All prices are in US dollars unless otherwise noted. Offers valid in US, void where prohibited by law or company policy, while supplies last.] VWR, the VWR logo and variations on the foregoing are registered (so or unregistered trademarks and service marks, of VWR International, LLC and its related companies. All other marks referenced are registered by their respective owner(s). [Visit vwr.com to view our privacy policy, trademark and additional dischainers. @2015 VWR International, LLC. All rights reserved.