

---

---

## Product Specifications

**VWR Part Number:** IR2108  
**ImmunoReagents, Inc. Part Number:** GtxHu-015-B

**Product:** GOAT X MYOGLOBIN IG FRACTION

**Concentration:** >10 mg/ml (E 1% at 280 nm = 1.3)

**Amount:** 1.0 ml

**Conjugate:** Unconjugated

**Form:** Clear, colorless liquid, 0.2 µm filtered

**Purification:** Proprietary 2-step fractionation procedure

**Purity:** > 80% based on SDS-PAGE

**Host:** Goat

**Immunogen:** Purified Human Cardiac Myoglobin

**Buffer:** 10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2

**Storage:** 2-8 °C

**Shelf Life:** 1 year from date of receipt. Prepare working dilution prior to use and then discard.

**Specificity:** Human Cardiac Myoglobin

**Cross Reactivity:** Human Skeletal Myoglobin

**Country of Origin:** Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.

**Applications:** This antibody is suitable for all immunoassay applications. The optimal working dilution should be determined by the investigator.

**Disclaimer:** For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.