



Accelerate your sample measurement

Purchase a new Orion Versa Star Pro benchtop meter and receive an additional measurement module for free*

Thermo Scientific™ Orion™ Versa Star Pro™ meters deliver outstanding performance and flexibility in the lab, featuring four channels that can be customized for your measurements.

- Modules for measurement of pH, ISE, conductivity, or dissolved oxygen are automatically recognized by the Orion Versa Star Pro meter and can be added or removed at any time
- The large color display can be personalized to show only the information you need and to display one to four measurements simultaneously in any combination
- Setup and calibration is designed to be fast and simple with step-by-step instructions and a numeric keypad
- Meter interface can be customized in a variety of languages



Limited-time savings
Offer ends June 30

Enjoy the versatility of an Orion Versa Star Pro meter in your lab

Purchase a qualifying Orion Versa Star Pro meter or kit from the list below by calling 1.800.932.5000, visiting vwr.com or contacting your VWR sales representative between January 1, 2019 and June 30, 2019 and **receive a module for free** for measurement of pH/ISE, conductivity, or dissolved oxygen.

To get your free module, have your VWR purchase order, VWR invoice or VWR packing slip ready and fill out the online form at vwr.com/promotions and search for **Promo Code 4161** before July 31, 2019.


Please allow up to eight weeks for delivery of your free product.



Ordering information

Product	Cat. No.
Qualifying Orion Versa Star Pro meters and kits	
Orion Versa Star Pro pH meters	
Meter with pH module	89206-378
Meter kit with pH module, 8302BNUMD Orion ROSS Ultra Triode pH/ATC electrode, Orion Star stirrer probe, ROSS pH buffer and solution kit	89206-380
Meter with pH/LogR module, ATC probe	89206-402
Meter kit with pH/LogR module, 8172BNWP Orion ROSS Sure-Flow pH electrode, ATC probe, ROSS pH buffer and solution kit	89206-404
Orion Versa Star Pro conductivity meters	
Meter with conductivity module	89206-382
Meter kit with conductivity module, 013005MD conductivity probe, 1413 µS/cm conductivity standard	89206-384
Orion Versa Star Pro dissolved oxygen meters	
Meter with DO/RDO module	89206-386
Meter kit with DO/RDO module, 083005MD DO probe, DO probe maintenance kit, BOD adapter/funnel/stirrer	89206-388
Orion Versa Star Pro pH/ISE meters	
Meter with pH/ISE module	89206-390
Meter kit with pH/ISE module, 8102BNUWP ROSS Ultra pH electrode, ATC probe, Orion Star stirrer probe, ROSS pH buffer and solution kit	89206-392
Meter with 2 pH/ISE modules	89206-394
Meter kit with 2 pH/ISE modules, 8102BNUWP ROSS Ultra pH electrode, ATC probe, Orion Star stirrer probe, ROSS pH buffer and solution kit, second electrode stand	89206-396
Orion Versa Star Pro pH, conductivity meters	
Meter with pH and conductivity modules	89206-398
Meter kit with pH and conductivity modules, 8157BNUMD ROSS Ultra Triode pH/ATC electrode, 013005MD conductivity probe, ROSS pH buffer and solution kit, 1413 µS/cm conductivity standard	89206-400
Orion Versa Star Pro pH/ISE, conductivity, dissolved oxygen meters	
Meter with pH/ISE, conductivity and DO/RDO modules	89206-406
Meter with pH/ISE, pH/ISE, conductivity and DO/RDO modules	89206-410
Meter kit with pH/ISE, conductivity and DO/RDO modules, 8157BNUMD ROSS Ultra Triode pH/ATC electrode, 013005MD conductivity probe, 083005MD DO probe, Orion Star stirrer probe, ROSS solution kit, 1413 µS/cm conductivity standard, DO probe kit, BOD adapter/funnel/stirrer	89206-408
Meter kit with pH/ISE, pH/ISE, conductivity and DO/RDO modules, 8157BNUMD ROSS Ultra Triode pH/ATC electrode, 013005MD conductivity probe, 083005MD DO probe, Orion Star stirrer probe, ROSS solution kit, 1413 µS/cm conductivity standard, DO probe kit, BOD adapter/funnel/stirrer	89206-412

The above meters include an electrode stand, universal power adapter, literature and USB cable.

1.800.932.5000 | VWR.COM

Prices and product details are current when published and subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR, part of Avantor, makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC and/or Avantor, Inc. or affiliates. All prices are in US dollars unless otherwise noted. Offers valid in US and Canada, void where prohibited by law or company policy, while supplies last. | Trademarks are owned by Avantor, Inc. or its affiliates, unless otherwise noted. | Visit vwr.com to view our privacy policy, trademark owners, and additional disclaimers. © 2019 Avantor, Inc. All rights reserved.