

Engineered for Protection. Designed for Comfort.

KIMTECH PURE* G3 Sterile STERLING* Nitrile Gloves

KIMBERLY-CLARK* has developed a low-cost sterile nitrile glove combining the sensitivity of latex with the protection of nitrile. Our innovative STERLING* gloves manufacturing technology enables us to deliver a comfortable and affordable glove with all the protection and cleanliness our customers have come to expect.

When double-donned, the KIMTECH PURE* G3 Sterile STERLING* Nitrile Gloves deliver the equivalent feel & dexterity of a single latex glove without the risk of Type I latex allergic reactions. Protection has never been so comfortable.

The KIMTECH PURE* G3 Sterile STERLING* Nitrile Glove is also environmentally responsible. We have improved packaging to deliver 50% more gloves per case than traditional gloves. Average use of 25 cases per month results in reduction of 1 ton of waste per year vs. traditional latex gloves.

Calculate Your Saving:
www.kimtech.com/sterlingcalculator



KIMTECH

PURE* BRAND



Quality Standards

- PPE Category III product classified by EC Council Directive 89/686/EED
- Tested in accordance with EN Norms EN 420-2003
- Cleanroom packaged to meet the needs of Class 10 Cleanrooms
- Meets or exceeds AQL level of 1.5 for pinholes
- Manufactured in accordance with quality System ISO 9001

Cleanliness Characteristics

Parameter	Limit	Test Method
Particles		
Per cm ² ≥ 0.5 micron	1200	TEST-RP-CC005

Physical Properties

Characteristics	Value								Test Method
Freedom from Holes	1.5 AQL ¹								ASTM D 5151
Tensile Properties	Tensile Strength				Ultimate Elongation				ASTM D 412 and ASTM D 573
Before Aging	42 MPa, nominal				650%, nominal				
After Accelerated Aging	38 MPa, nominal				550%, nominal				
Dimensional	Measured Point				mm		mil		ASTM D 3767 and ASTM D 6319
Nominal Thickness	Middle Finger				0.10		3.9		
Palm	0.08				3.1				
Cuff	0.07				2.8				
Nominal Length	305mm / 12 inches								
Palm Widths	6	6.5	7	7.5	8	8.5	9	10	ASTM D 3767 and ASTM D 6319
Nominal Width (mm)	80	87	94	98	109	114	120	128	
Endotoxin	(Maximum)								LAL Kinetic Turbidimetric Method
Endotoxin Units/pair	20								

50% LESS BULK THAN
TRADITIONAL LATEX
STERILE GLOVES

LATEX-FREE

4.0 MIL THICKNESS

12" LENGTH

STATIC DISSIPATIVE IN USE

WALLEDED AND POUCHED
IN POLYETHYLENE

PACKAGED FOR
ASEPTIC DONNING

COA, COI AND TREND DATA
AVAILABLE ONLINE

KIMTECH PURE [®] G3 Sterile STERLING [®] Nitrile Gloves										Packaged to Meet the Needs of a Class 10 Cleanroom	
Size		6	6.5	7	7.5	8	8.5	9	10	Pairs/Bags	Total/Case
KIMTECH PURE [®] G3 Sterile	KCP Code	11821	11822	11823	11824	11825	11826	11827	11828	30	300
STERLING [®] Nitrile Gloves - 12"	VWR Cat. No.	89135-370	89135-372	89135-374	89135-376	89135-378	89135-380	89135-382	89135-384		

To order, contact your VWR Sales Representative, visit vwr.com, or call 1.800.932.5000 today.

Our Guarantee

Your total satisfaction means everything to us. If, for any reason, our products do not meet your expectations, Kimberly-Clark will reimburse you for your initial purchase, via FREE product, for up to \$1,000.

Reduce Today, Respect Tomorrow[®] is the KIMBERLY-CLARK PROFESSIONAL[®] approach to sustainability. It begins with the understanding that the way we use resources today shapes the world of tomorrow. And it has led us to focus on reducing consumption at every stage of the product lifecycle – from design and manufacture to distribution and disposal. Reduction is the key to lowering the environmental impact of our activities as well as those of customers. To learn more, visit www.kcpreducetoday.com/us



Kimberly-Clark warrants that its products comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers. Except to the extent prohibited by applicable law: 1) **THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE;** 2) K-C is not liable for any kind of special, incidental, or consequential damages; and 3) K-C's liability for breach of contract, tort, or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

©/® Trademarks of Kimberly-Clark Worldwide, Inc. or its affiliates. Marques déposées de Kimberly-Clark Worldwide, Inc. ou de ses filiales. © 2010 KCWW. K02067 K4663-10-01 6/10



Prices, product appearance and specifications are current at the time of printing, subject to change without notice. Availability for certain products may be limited by federal, state, provincial or local licensing requirements. VWR makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in U.S. dollars unless otherwise noted. Offers valid in USA and Canada, void where prohibited by law or company policy, while supplies last. Visit vwr.com to view our privacy policy and additional disclaimers.

VWR, forms of VWR, and the VWR logo and/or design are either registered trademarks ®, trademarks ™, or service marks ℠ of VWR International, LLC in the United States and/or other countries. All other marks referenced herein are registered trademarks, trademarks or service marks of their respective owner(s). For a complete list of trademark owners please visit vwr.com.

©2010 VWR International, LLC. All rights reserved.

0710 Lit. No. POD 11021