SPEAKMAN® SE-616

COMBINATION SHOWER & EYEWASH

DESCRIPTION

The SE-616 Safe-T-Zone[®] features the SE-505 eyewash with two aerated sprays and stainless steel bowl combined on a powder coated galvanized steel stanchion with an impeller action deluge showerhead which is activated by a high visibility yellow pull rod.

SPECIFICATIONS

Showerhead: 8" diameter Cycolac[®] yellow plastic Flow Control: Internal 20 gpm regulator Valve: 1" NPT female brass, chrome plated. Full flow stay-open ball valve Activator: Powder coated yellow, aluminum triangular pull rod Stanchion: 1¹/4" IPS galvanized steel piping with brass fittings Inlet & Waste: 1¹/4" NPT female Performance: 20 gpm @ 30 psi Finish: DuraJade[™] powder coated finish

EYEWASH: SE-505

Bowl: 505 series stainless steel Spray Heads: (2) aerated yellow nylon spray outlets Valve: ¹/₂" NPT female brass, chrome-plated. Full flow stay-open ball valve Activator: Stainless steel trigger bar Shrouds: Yellow polypropylene Performance: 3.0 gpm @ 30 psi Compliance: ANSI Z358.1 Universal Emergency Sign Included

OPTIONS

- □ 30GPM 30gpm regulator
- HFO Hand foot operation
- FPVFreeze protection valve
- SPVScal protection valve
- Image: FLWFlow switch
- HS Hand held spray
- TS Top supply
- SSH
 Stainless steel showerhead
- SPRStainless steel pull rod
- SSBVStainless steel ball valves
- BH Chrome plated brass showerhead

Job Name
Location
Architect/Engineer
Sales Representative
Wholesaler
Date Model #

24″

(610mm)

69″ MAX. TO FLOOR

(1753mm)

NOTE: PULL HANDLE

SHOWN ROTATED 90°

7'-0"

TO FLOOR

(2134mm)

42" (1067mm) 1 1/4" NPTF

5'-5"

TO FLOOR

(1651mm)

1 1/4" NPTF

WASTE

6" (152mm)

INLET