

NBP2-03934**RFC2 Antibody (4C11)****Unit Size**

0.1 ml

Concentration

Please see the vial label for concentration.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, FLOW, IHC, IHC-P

Species

Human

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Purity

Affinity purified

Preservative

0.02% Sodium Azide

Immunogen

Human recombinant protein fragment corresponding to amino acids 1-234 of human RFC2 (NP_002905) produced in E.coli.

Recommended Dilutions


Western Blot 1:2000, Immunohistochemistry-Paraffin 1:150, Flow Cytometry 1:100, Immunohistochemistry

Buffer

PBS (PH 7.3) containing 1% BSA, 50% glycerol

Images (more available at www.novusbio.com/NBP2-03934)

Western Blot: RFC2 Antibody (4C11) [NBP2-03934] - HEK293T cells were transfected with the pCMV6-ENTRY control (Left lane) or pCMV6-ENTRY RFC2 (Right lane) cDNA for 48 hrs and lysed. Equivalent amounts of cell lysates (5 ug per lane) were sep... See more at www.novusbio.com/NBP2-03934



Immunohistochemistry-Paraffin: RFC2 Antibody (4C11) [NBP2-03934] Staining of paraffin-embedded Human tonsil using anti-RFC2 mouse monoclonal antibody.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

