

NBP1-99376**IGFBP3 Protein****Unit Size**

0.025 mg

Concentration

Lyoph

Storage

Store at -20C. Avoid freeze-thaw cycles.

Species

Human

Purity

>95% pure by SDS-PAGE

Specificity/Sensitivity

Unit Definition:N/A

Immunogen

Source: E. coli

Endotoxin Level: <0.1 ng/ug

Activity (Specifications/test method):N/A

Biological activity:The EDSO as determined by its ability to inhibit IGF-II induced proliferation of MCF-7 is <0.2 , in the presence of 15 ng/ml of human IGF-II.

Results:<0.2

Binding Capacity:N/A

Buffer

Sterile filtered and lyophilized from 20 mM HCl

Reconstitute in H₂O to a concentration of 0.1-1.0 . The solution can then be diluted into other aqueous buffers and store at 4C for 1 week or -20C for future use.**Images**

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-99376

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

