

NBP1-89875**IL2 ELISA Kit****Unit Size**

96 Tests

Concentration

Concentration is not relevant for this product.
 Please see the protocols for proper use of this product.

Storage

Store at 4C. Do not freeze.

Immunogen

Suitable Sample Types: Cell culture supernatant, serum, plasma (EDTA, citrate, heparin), amniotic fluid, urine, white blood
 Sensitivity: 9.9 pg/mL Standard Curve Range: 18.8 - 1,200 pg/mL

Uses

The human IL-2 ELISA is an enzyme-linked immunosorbent assay for the quantitative detection of human IL-2

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-89875

Notes

Components Included:

Aluminium pouch(es) with a Microwell Plate coated with monoclonal antibody to human IL-2
 1 vial (100 ul) Biotin-Conjugate anti-human IL-2 polyclonal antibody

Streptavidin-HRP

Human IL-2 Standard lyophilized, 2.4 ng/ml upon reconstitution

Control high

, lyophilized

Control low

, lyophilized

Sample Diluent

Wash Buffer Concentrate ... See more at www.novusbio.com/NBP1-89875

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

