

NBP1-77310**TEM1 Antibody****Unit Size**

0.1 mg

Concentration

1 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA, IHC, IHC-P

Species

Human, Mouse, Rat

Molecular Weight

81kDa

Host

Rabbit

Clonality

Polyclonal

Purity

Peptide affinity purified

Preservative

0.02% Sodium Azide

Specificity/Sensitivity

At least two isoforms of TEM1 are known to exist; this antibody recognizes both isoforms.

Immunogen

Antibody was raised against a 14 amino acid peptide near the carboxy terminus of the human TEM1 (NP_065137).

Recommended Dilutions



ELISA, Immunohistochemistry, Immunohistochemistry-Paraffin 2.5 ug/ml, Western Blot 0.5-1 ug/ml

Buffer

PBS

Uses

Although not tested this antibody may be useful in Immunofluorescence/Immunocytochemistry.

ImagesWestern Blot: TEM1 Antibody [NBP1-77310] - Human colon tissue lysate with TEM1 antibody at (A) 0.5 and (B) 1 ug/ml. Immunohistochemistry-Paraffin: TEM1 Antibody [NBP1-77310] - Human colon tissue with TEM1 antibody at 2.5 ug/ml. 

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

