

**NBP1-75401****Goat anti-Rat IgG, H/L Chains Antibody [FITC]****Unit Size**

2 mg

**Concentration**

1.0 mg/ml

**Storage**

Store at 4°C. Do not freeze.

**Applications**

FLOW, IM

**Species**

Rat

**Host**

Goat

**Clonality**

Polyclonal

**Isotype**

IgG

**Conjugate**

FITC

**Purity**

Affinity purified

**Preservative**

0.05% Sodium Azide

**Specificity/Sensitivity**

Based on IEP, this antibody reacts with: heavy chains on rat IgG and light chains on all rat immunoglobulins.

**Immunogen**

Purified Rat IgG (H&amp;L)

**Recommended Dilutions**

immunomicroscopy 1:20-1:2000

Flow Cytometry 1:20-1:2000

**Buffer**

10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA, Protease/IgG free

**Uses**

This conjugate is suitable for immunomicroscopy and flow cytometry.

**Images**This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NBP1-75401](http://www.novusbio.com/NBP1-75401)**Notes**

Purity &gt; 95% based on SDS-PAGE. Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.

Updated 3/9/2013 2.0

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).*

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

