

NBP1-50176**SRPX2 Antibody****Unit Size**

0.05 mg

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at 4°C short term. Aliquot and store at -80°C long term. Avoid freeze-thaw cycles.

Applications

IHC, IHC-P

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.1% Sodium Azide

Specificity/Sensitivity

Human SRPX2

Immunogen

C-terminal domain of human.

Recommended Dilutions

Immunohistochemistry, Immunohistochemistry-Paraffin 10 ug/ml

Buffer

PBS

Uses

This antibody is useful in Immunohistochemistry-Paraffin .

Images

Immunohistochemistry-Paraffin: SRPX2 Antibody [NBP1-50176] - Staining of human brain, cortex. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody concentration 10 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

