

NBP1-45376**Bcl3 Antibody****Unit Size**

0.1 mg

Concentration

0.2 mg/ml

Storage

Aliquot and store at -20C or -80C. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-Fr, IHC-P, IP

Species

Human, Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Purity

Affinity purified

Preservative

0.01% Thimerosal

Immunogen

Synthetic peptide surrounding amino acid 424 of human Bcl-.

Recommended Dilutions
 Immunohistochemistry
 Immunohistochemistry-Frozen
 Immunohistochemistry-Paraffin
 Immunoprecipitation
 Western Blot 2-4 ug/ml
Buffer

phosphate-buffered saline (PBS) containing 30% glycerol, 0.5% BSA

Uses

Western blot analysis (2-4ug/ml) Per researchers feedback, the antibody also works well in Immunoprecipitation (10-20 ug/ml), and Immunohistochemistry (20-40 ug/ml). However, the optimal conditions should be determined individually. Detects 55-60 kDa Bcl-3 of human, mouse, and rat origins. Other species have not been tested.

Images
 Western Blot: Bcl3 Antibody [NBP1-45376] -
 Western blot
 analysis of BCL-3 in
 Jurkat cell lysate.


Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA
 8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com
Novus Canada
 461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com
Novus Europe
 12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com
