

NBP1-44473**TSSC3 Protein****Unit Size**

0.05 mg

Concentration

0.5 mg/ml

Storage

Store at -80C. Avoid freeze-thaw cycles.

Applications

ELISA, PAGE

Species

Human

Purity

Protein

Preservative

No Preservative

Specificity/Sensitivity

This is a TSSC3 Protein (1-152aa). Human recombinant protein expressed in E.coli. His tag increases size to 172aa

Immunogen

MGSSHHHHHH SSGLVPRGSH MKSPDEVLR GELEKRSDSL FQLWKKKRGV
 LTSDRLSLFP ASPRARPKEL RFHSILKVDC VERTGKYVYF TIVTTDHKEI DFRGAGESCW
 NAAIALALID FQNRRLQDF RSRQERTAPA APAEDAVAAA AAAPSEPSEP
 SRPSPQPKPR TP

Recommended Dilutions

ELISA

SDS-Page

Buffer


20mM Tris-HCl buffer (pH8.0) containing 20% glycerol 0.1M NaCl, 1mM DTT

Uses

This product is useful for ELISA and SDS-Page. The purity of this protein is > 80% by SDS - PAGE. This recombinant protein was expressed in E.Coli bacteria. The endotoxin levels of this protein have not yet been determined.

Images

SDS-Page: TSSC3 Protein [NBP1-44473] -
 PHLDA2, 19.2 kDa (172aa) with a purity of 80% by
 SDS - PAGE



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

