

NBP1-30208**UBE2S Protein****Unit Size**

0.1 mg

Concentration

1.0 mg/ml

Storage

Store at -80C. Avoid freeze-thaw cycles.

Applications

ELISA, PAGE

Species

Human

Purity

Protein

Preservative

No Preservative

Specificity/Sensitivity

Human, His-tagged, Recombinant UBE2S, 1-222 aa

Immunogen

UBE2S, 1-222 aa, Human, His-tagged, Recombinant, E.coli (NP_055316.2).

Recommended Dilutions

ELISA

SDS-Page

Buffer


20 mM Tris-HCl buffer (pH8.0) containing 1mM DTT and 20% glycerol

Uses

The purity of this protein is > 90% by SDS - PAGE. This recombinant protein was expressed in E.Coli bacteria. The endotoxin levels of this protein have not yet been determined.

Images

SDS-Page: UBE2S Protein [NBP1-30208] - UBE2S, 27.9 kDa (258aa), confirmed by MALDI-TOF with a purity of 90% by SDS - PAGE



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

