

NBP1-25973**VGluT3 Antibody****Unit Size**

0.1 ml

Concentration

lyoph

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-Fr, IHC-P

Species

Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Purity

Whole antisera

Preservative

No Preservative

Immunogen

A synthetic peptide from the c-terminal region of mouse VGLUT3 conjugated to an immunogenic carrier protein was used as the immunogen.

Recommended Dilutions

Western Blot 1:300 to 1:2000, Immunohistochemistry-Paraffin, Immunohistochemistry-Frozen 1:300 to 1:2000, Immunohistochemistry

Buffer

Lyophilized Reconstitute in 0.1 ml of sterile water. Centrifuge to remove any insoluble material. When reconstituting, glycerol (1:1) may be added for an additional stability.

Uses

Immunohistochemistry-Paraffin/Frozen and Western Blot

Images (more available at www.novusbio.com/NBP1-25973)

Western Blot: VGLUT3 Antibody [NBP1-25973] - mouse brain lysate (10% gel, 1:29; reduced, denatured) using Rabbit antibody to c-terminal region of mouse VGluT3: whole serum at 1:500 dilution; blocked with 1% LFD for 15 minutes at room temper... See more at www.novusbio.com/NBP1-25973



Immunohistochemistry: VGluT3 Antibody [NBP1-25973] - IHC on rat spinal cord (free floating sections) using Rabbit antibody to c-terminal region of VGluT3 (Vesicular glutamate transporter 3): whole serum at 1 : 300 dilution incubated overnight... See more at www.novusbio.com/NBP1-25973



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

