

**NBP1-19118****VPS4B Antibody****Unit Size**

0.1 ml

**Concentration**

1.0 mg/ml

**Storage**

Store at 4C. Do not freeze.

**Applications**

IP, WB (-)

**Species**

Human

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Immunogen affinity purified

**Preservative**

0.09% Sodium Azide

**Immunogen**

The immunogen recognized by this antibody maps to a region between residue 300 and 350 of human vacuolar protein sorting 4 homolog B using the numbering given in entry NP\_004860.2 (GeneID 9525).

**Recommended Dilutions**

Immunoprecipitation 2 -5 ug/mg lysate

Western Blot (Negative)

**Buffer**


Tris-citrate/phosphate buffer, pH 7 to 8

**Uses**

This antibody is useful for immunoprecipitation. It is not recommended for western analysis.

**Images**

Immunoprecipitation: VPS4B Antibody [NBP1-19118] - Whole cell lysate (1 mg for IP, 20% of IP loaded) from HeLa cells. Affinity purified rabbit anti-VPS4B antibody used for IP at 3 mcg/mg lysate. VPS4B was also immunoprecipitated by rabbit an... See more at [www.novusbio.com/NBP1-19118](http://www.novusbio.com/NBP1-19118)



Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

