

**NB900-66730****10X EDTA buffer pH 8.0****Unit Size**

500 ml

**Concentration**

Concentration is not relevant for this product.  
 Please see the protocols for proper use of this product.

**Storage**

Store at room temperature.

**Applications**

IHC-P

**Preservative**

No Preservative

**Specificity/Sensitivity**

10x EDTA Buffer pH 8.0 for Heat Induced Epitope Recovery

**Recommended Dilutions**

Immunohistochemistry-Paraffin

**Buffer**

Dilute one part buffer with nine parts de-ionized or distilled water.

**Uses**

To recover antigens masked by over fixation in cross linking fixatives such as formalin.

1. Deparaffinize and bring tissue section to buffer.
2. Fill the plastic coplin jar with the antigen unmasker solution.
3. Place the jar in the in steamer or water bath.
4. Preheat steamer or water bath containing coplin jars to 95-100 C.
5. Place the deparaffinized slides (1 to 3 ... See more at [www.novusbio.com/NB900-66730](http://www.novusbio.com/NB900-66730)

**Images**

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NB900-66730](http://www.novusbio.com/NB900-66730)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

