

NBA1-28367

Mouse IgE, kappa L Chain Isotype Control (MEA-36)

Unit Size

0.1 mg

Concentration

Concentration is not relevant for this product.
Please see the protocols for proper use of this product.

Storage

Store at 4C. Do not freeze.

Species

Mouse

Host

Mouse

Clonality

Monoclonal

Isotype

IgE, Kappa

Purity

Affinity purified

Preservative

0.09% Sodium Azide

Specificity/Sensitivity

The isotype of MEA-36 immunoglobulin is mouse (BALB/c) IgE, kappa. This antibody reacts with Trinitrophenol (TNP) only. This monoclonal antibody was chosen as an isotype control after screening on a variety of resting, activated, live, and fixed mouse, rat and human tissues. It is useful as a standard in mouse IgE ELISA.

Immunogen

Trinitrophenol and KLH.

Recommended Dilutions

ELISA
Flow Cytometry
Western Blot

Buffer

Phosphate-buffered solution, pH 7.2

Uses

Each lot of this antibody is quality control tested by ELISA and SAS-PAGE to assure the isotype and purity, and the purity is greater than 95%. Use at concentrations comparable to those of the specific antibody of interest.

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBA1-28367

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

