

NB600-235H**Blimp-1 Antibody (3H2-E8) [HRP]****Unit Size**

0.1 ml

Concentration

1.0 mg/ml

Storage

Store at 4C in the dark.

Applications

WB

Species

Human, Mouse, Porcine

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Conjugate

HRP

Purity

Protein G purified

Preservative

No Preservative

Specificity/Sensitivity

This is specific for the Blimp-1.

Immunogen

A fragment of the mouse Blimp-1 (residues 199-409).

Recommended Dilutions

Western Blot 1:1000

Buffer

PBS

Uses

This antibody is useful for ELISA, Immunofluorescence, Western Blot, Immunocytochemistry, Immunohistochemistry-Paraffin and Immunoprecipitation. By WB, this antibody recognizes a band ~98 kD and may recognize one ~80 kDa (the beta form). Though this production of antibody has not been tested, previous lots have been used for Immunohistochemistry-Paraffin, immunocytochemistry, and immunofluorescence... See more at www.novusbio.com/NB600-235H

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB600-235H

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

