

NB600-423**MLH1 Antibody [Agarose Immobilized]****Unit Size**

0.1 mg

Concentration

Please see the vial label for concentration.

Storage

Store at 4C. Do not freeze.

Applications

IP

Species

Human

Host

Rabbit

Clonality

Polyclonal

Conjugate

Agarose Immobilized

Purity

Immunogen affinity purified

Preservative

0.1% Sodium Azide

Immunogen

Rabbit anti-human MLH1 affinity purified Antibodies were coupled to agarose beads using a cyanogen bromide method.

Recommended Dilutions

immunoprecipitation 15-25 ul gel per 0.1-1 mg of protein lysate/extract

Buffer

Phosphate Buffered Saline (PBS)

Uses

This antibody is useful for Immunoprecipitation. The investigator should determine the optimal working dilution for a specific application.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB600-423

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

