

NB120-10398**CCR6 Antibody (53103.111)****Unit Size**

0.1 mg

Concentration

0.5 mg/ml

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

FLOW

Species

Human

Host

Mouse

Clonality

Monoclonal

Isotype

IgG2b

Purity

Protein G purified

Preservative

No Preservative

Specificity/Sensitivity

Human CCR6 reacts with CCR6 transfected cells and not with the parent cell line by flow cytometry. The shows no cross-reactivity with CCR1, CCR2, CCR3, CCR4, CCR5, CCR7, CXCR1, CXCR2, CXCR3, CXCR4 and STRL33 transfected cells.

Immunogen

Human CCR6 transfected NSO mouse myeloma cells.

Recommended Dilutions

Flow Cytometry

Buffer

PBS Endotoxin level is less than 10 ng per mg antibody

Uses

Flow Cytometry Use 5ug for 10⁵ cells. (Determined using human CCR-6 on peripheral blood mononuclear cells (PBMC)). Not tested in other applications. Optimal dilutions/concentrations should be determined by the end user.

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB120-10398

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

