

NB120-15109**Dysferlin Antibody****Unit Size**

7.0 ml

Concentration

Please see the vial label for concentration.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-P

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.1% Sodium Azide

Specificity/Sensitivity

Dysferlin

Immunogen

Synthetic peptide (unfortunately, the amino acid sequence is considered to be commercially sensitive) (Human) (C terminal).

Recommended Dilutions

Immunohistochemistry-Paraffin Neat, Western Blot, Immunohistochemistry

Buffer

PBS, BSA - Prediluted antibody

Uses

This product is useful for Immunohistochemistry Paraffin, Western Blot. If a 6mL or 7mL pre-diluted size is purchased this product can be used Neat (without further dilution). Use recommended dilution for the concentrated vials only.

Images

Western Blot: Dysferlin Antibody [NB120-15109] - Skeletal Muscle

Immunohistochemistry-Paraffin: Dysferlin Antibody [NB120-15109] - Human skeletal muscle



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

