

NB120-49254**TWIST1 Antibody****Unit Size**

0.1 mg

Concentration

Lyoph

Storage

Aliquot and store at -20C or -80C. Avoid freeze-thaw cycles.

Applications

WB, ELISA, IHC-P

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Protein A purified

Preservative

No Preservative

Specificity/Sensitivity

TWIST1

Immunogen

A synthetic peptide corresponding to a region of human TWIST1 with an internal ID of P20171.

Recommended Dilutions

ELISA, Immunohistochemistry-Paraffin, Western Blot

Buffer

PBS & 2% Sucrose lyophilized with the antibody. Centrifuge the vial of lyoph antibody at 12,000 x g for 20 seconds. Add 100ul of distilled water. Vortex followed by centrifuge again to pellet the solution. Final concentration is 1 mg/ml in PBS buffer

Uses

ELISA: Use at an assay dependent dilution. ELISA titre: 1/1,562,500. WB: Use at a concentration of 2.5

Images

Western Blot: TWIST1 Antibody [NB120-49254] - Jurkat cell lysate, Antibody Titration: 2.5ug/ml



Immunohistochemistry-Paraffin: TWIST1 Antibody [NB120-49254] - Human Uterus Tissue, 4-8ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

