

NB120-6821

Donkey anti-Mouse IgG Antibody [Alkaline Phosphatase]

Unit Size

1.0 mg

Concentration

1 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

WB, ELISA, IHC, IHC-P

Species

Mouse

Host

Donkey

Clonality

Polyclonal

Isotype

IgG

Conjugate

Alkaline Phosphatase

Purity

IgG purified

Preservative

0.01% Sodium Azide

Specificity/Sensitivity

Assay by immunoelectrophoresis resulted in a single precipitin arc against anti-Alkaline Phosphatase (calf intestine), anti-Donkey Serum, Mouse IgG, and Mouse Serum.

Immunogen

Mouse IgG whole molecule

Recommended Dilutions

ELISA 1:2000 - 1:10000, Immunohistochemistry 1:200 - 1:1000, Western Blot 1:500 - 1:2500, Immunohistochemistry-Paraffin

Buffer

0.05M Tris Chloride, 0.15M Sodium Chloride, 0.001M Magnesium Chloride, 0.0001M Zinc Chloride

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB120-6821

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

