

NB200-193R**MMP2 Antibody [DyLight 550]****Unit Size**

0.1 ml

Concentration

1.0 mg/ml

Storage

Store at 4C in the dark.

Applications

WB, ELISA, IHC, IHC-Fr, IHC-P

Species

Human, Mouse, Rat, Chicken

Host

Rabbit

Clonality

Polyclonal

Conjugate

DyLight 550

Purity

Peptide affinity purified

Preservative

No Preservative

Specificity/Sensitivity

This is specific for pro and active forms of MMP-2. It does not react with other MMPs tested.

ImmunogenA synthetic peptide corresponding to residues 475-490 of human MMP-2:
MGPLLVA^TFWPELPEK**Recommended Dilutions**

ELISA, Western Blot, Immunohistochemistry-Paraffin 2-4 ug/ml, Immunohistochemistry-Frozen 2-4 ug/ml, Immunohistochemistry

Buffer

50mM sodium borate

Uses

NB 200-193 may be used for Western blotting, where two bands are seen between 66 and 72 kDa, representing the MMP-2 band-pair. In addition, this antibody may be used for immunohistochemistry on frozen and/or paraffin-embedded tissues, without antigen retrieval. ELISA has only been tested on the peptide.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB200-193R

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA
 8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com
Novus Canada
 461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com
Novus Europe
 12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com
