

NB110-79875G**SOX2 Antibody [DyLight 488]****Unit Size**

0.1 mg

Concentration

1.0 mg/ml

Storage

Store at 4C in the dark.

Applications

WB

Species

Human, Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Conjugate

DyLight 488

Purity

Immunogen affinity purified

Preservative

No Preservative

Marker

Embryonic Stem Cell Marker

Specificity/Sensitivity

SOX-2

Immunogen

Reacts with residues 113-127 of the 37 kDa (predicted molecular weight is 34 kDa) human, mouse and rat SOX-2 protein. Sequence is 100% conserved in most species.

Recommended Dilutions

Western Blot

Buffer

PBS

Uses

Western Blot

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-79875G

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

