

NB110-82364**TRPM2 Antibody****Unit Size**

0.1 ml

Concentration

1.5 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB

Species

Mouse, Rat

Molecular Weight

172kDa

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.1% Sodium Azide

Immunogen

Synthetic peptide made to an internal portion of the mouse TRPM2 protein (within residues 1200-1300). [Swiss-Prot# Q91YD4]

Recommended Dilutions

Western Blot 2.0 mg/ml

Buffer


PBS, 30% glycerol

Uses

This TRP7 antibody is useful in Western blot, where a band is seen at ~172 kDa.

Images

Western Blot: TRPM2 Antibody [NB110-82364] - Detection of TRPM2 in mouse brain membrane lysates using NB110-82364.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

