

**NB110-7545****Respiratory Syncytial Virus Antibody (9C5)****Unit Size**

0.2 mg

**Concentration**

4.0 mg/ml

**Storage**

Store at 4C. Do not freeze.

**Applications**

ELISA

**Species**

Virus

**Host**

Mouse

**Clonality**

Monoclonal

**Isotype**

IgG2b

**Purity**

Protein G purified

**Preservative**

0.1% Sodium Azide

**Specificity/Sensitivity**

RSV F protein specific. Highly reactive with the surface domains of both mature RSV virions and empty virion envelopes without formed inner nucleocapsid structures.

**Immunogen**

Full length native protein (purified RSV, strain long).

**Recommended Dilutions**

ELISA assay dependent

**Buffer**

PBS pH 7.4

**Uses**

ELISA

**Images**This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NB110-7545](http://www.novusbio.com/NB110-7545)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

